



Two Indication Type F Color Light Dwarf Signal

## Type F Color Light Dwarf Signals

**Note:** See foreword and order information, page 240, at the beginning of this part.

Unless otherwise specified, Dwarf Signals are furnished with lenses that give a 20° upward spread.

Where the source of current supply is alternating current, we recommend the use of a small transformer as shown on Plate P0102, Fig. B in each lamp case. These transformers will be assembled in the lamp cases before shipment when specified.

Drawing references are shown for convenience in checking shipping lists and invoices.

Fig. No.	Name	Drawing Reference
<b>Order by plate, figure number and name</b>		
A	Type F Two-indication, Color-light Dwarf Signal Complete, equipped with 5" doublet lenses and arranged for adjustable mounting. Does not include lamp bulbs nor transformers.....	
A1	as above, except unit only with mounting socket Fig. 16 and without base Fig. 17, for mounting on 2½" pipe.....	
1	Case Complete.....	27470-3
2	Glass, clear, with etched lines for front sight.....	924-4
3	Bezel Ring, with screws for glass Fig. 2.....	43718-1
4	Screw, No. 10—32x5/8" rd. hd. with nut and lock washer for fastening hood to case.....	
5	Disc, used as cover where sighting glass is not required.....	39719-4
6	Terminal Block Complete, with screws for mounting.....	
7	Connector Complete, with screw for mounting to terminal block.....	
8	Bolt, ½"—13x3½" sq. hd. with two hex. nuts for mounting case to base.....	
9	Plug, sighting, as shown.....	51364
10	Bolt, ½"—13x2" sq. hd. with two hex. nuts.....	
11	Plate, used as cover for top case.....	36761-1
12	Hood, as shown.....	49127-9
13	Transformer, Type K½. See Plate P0102, Fig. B for order reference.....	
14	Doublet Lens Unit Complete. For detail, see Plate H3001, Fig. B.....	36762-2

(Continued on following page)

# Type F Color Light Dwarf Signals

Drawing references are shown for convenience in checking shipping lists and invoices.

Fig. No.	Name	Drawing Reference
<b>Order by plate, figure number and name</b>		
15	Lamp Bulb, see Plate H3011 for order reference.....	
16	Mounting Socket Complete, as shown, for mounting Type F Color-light Signal Unit to 2½" pipe or to base Fig. 17.....	
17	Base, for use with mounting socket, Fig. 16, to provide an adjustable mounting for dwarf signals.....	21211-4